




KC-1261-S-12



특징 Feature

- 스톱 기구 부착품입니다. 스프링 스톱퍼를 누르면 정지가 해제되어 레일을 탈착할 수 있게 됩니다.
- 스테인레스제로 내식성이 뛰어납니다.
- 슬라이드부는 볼 베어링을 채용하여 움직임이 유연합니다.
- Equipped with stoppers. After pressing a spring stopper to unlock it, you can insert or remove a rail.
- Corrosion-resistant stainless is used.
- Slide section uses ball bearing so movement is smooth.

사양	● 재질: 냉간 압연 스테인레스 강판(SUS304) ● 표면 마무리: 경면 연마
용도	● 컴퓨터 주변기기·복사기·약품보관고·의료용 기기
비고	● 부착에는 M4 바인드 소나사 또는 트러스 소나사를 사용하십시오. ● 작동 불량 원인이 되므로 빼낸 이너 레일을 다른 레일에 삽입하지 마십시오. ● 본 제품을 오래 사용하기 위해서는 정기적으로 접동부에 윤활제를 도포해 주시기 바랍니다. (권장 윤활제: 리튬 비누기계 극압 그리스)

Specifications	● Material: Cold rolled stainless steel plate (SUS304) ● Finish: Mirror surface buffing
Specific-use	● Computer peripherals, OA and medical equipment.
Remarks	● Please use M4 binding head machine screws or truss head screws for installation. ● Do not place removed inner member in another rail; may prevent rail from operating properly. ● To prolong use, it is recommended that a lubricant be applied regularly to the sliding parts. (Recommended grease: Lithium-soap base extreme-pressure grease)

상품번호 Product No.	RoHS 10	L1	L2	P1	P2	P3	P4	P5	P6	N	(S)	허용 하중 N/pair Allowable load	제품질량(g) Mass	코드 Code	
KC-1261-S-12	●	304.8	300.8	260.3	247.6	136.5			152.4	9	224	314	304	22941	
KC-1261-S-14	●	355.6	351.6	311.1	298.4	187.3			203.2		275	284	360	22942	
KC-1261-S-16	●	406.4	402.4	361.9	349.2	238.1			254.0		315	353	404	22943	
KC-1261-S-18	●	457.2	453.2	412.7	400	288.9	200	406.4	203.2		330	422	455	22944	
KC-1261-S-20	●	508	504	463.5	450.8	339.7	225.4	457.2	228.6		11	381	392	507	22945
KC-1261-S-22	●	558.8	554.8	514.3	501.6	390.5	250.8	508	254			406	441	560	22946
KC-1261-S-24	●	609.6	605.6	565.1	552.4	441.3	276.2	558.8	279.4			432	441	614	22947
KC-1261-S-26	●	660.4	656.4	615.9	603.2	492.1	301.6	609.6	304.8			483	412	662	22948
KC-1261-S-28	●	711.2	707.2	666.7	654	542.9	327	660.4	330.2			493	412	710	22949

●: RoHS10 대응품 ▲: RoHS10에 대응 가능합니다.